

**MODEL: R4KPB23 - SLIM STAFF ASSIST CODE STATION**



R4KPB23

## FEATURES

- Two (2) call points with Call-Assurance LEDs and Monitor LED
- Back-lit pushbuttons for easy activation
- Cancel button
- Continuous supervision of station
- Plug-in connectors for easy service
- Output for elapsed timer
- Optional antimicrobial Bio-seal to cover buttons and allow for easy disinfecting of the station

## SPECIFICATIONS

**Power Required:** 7mA @ 15VDC

**Power Required when used with SLIM Speaker Module:**  
10 mA @ 15VDC

**Weight:** 0.20 lbs. (0.09 kg)

**Size: W:** 3.2" (8.1 cm)

**H:** 4.25" (10.8 cm)

**D:** 0.6" (1.5 cm) in back box: 0.5" (1.3 cm) off-wall

**Housing and Finish:** High-impact molded Cyclooy 2950 UL 94-5VB; light grey faceplate

**Controls/Indicators:** Two (2) Push button for call activation, One (1) Call-assurance LED, One (1) Call-assurance/Monitor LED, and One (1) Cancel button

**Terminations:** Plug-on connectors

**Backbox Requirement:** 1-gang, Non-gangable W: 2.25" (5.7 cm) H: 4" (10.2 cm) D: 3.5" (8.9 cm)

**Backbox Requirement when used with SLIM Speaker Module:** 3-gang, Non-gangable W: 5.5" (14 cm) H: 3.75" (9.5 cm) D: 3.5" (8.9 cm)

**Certification:** Designed for compliance to UL/C-UL 1069, FCC Part 15 Class B, IEC60601-1 and IEC60601-1-2, CE Marking (MDD), FDA Registration, RoHS Compliant

## DESCRIPTION

The Responder® 4000 SLIM Staff Assist Code Station is an emergency dual pushbutton station that has the ability to place two (2) unique call priorities from a single station. Using custom buttons, the station can be customized for unique call-ins such as: "Code Pink", "Push for Help", etc. This type of station is normally located at a patient room head wall for placing a call for help, staff emergency and/or code call. The Cancel button allows for cancellation of the call at the station. The station also provides an output for an elapsed timer.

The Staff Assist Code Station is connected to its associated corridor light and is continually supervised for station presence. Through programming, a "Trouble" message can annunciate at the associated console(s) when the station is removed from the system. This station also offers enhanced supervision capabilities by notifying staff if the cancel button is continuously depressed (stuck) for a long time. A "CB Fail" trouble message will annunciate at the associated console(s).

*Architect and Engineer (A&E) Specifications available online at: [customerconnection.rauland.com](http://customerconnection.rauland.com)  
Specifications subject to change without notice*

©Copyright 2009 Rauland-Borg Corporation Printed in USA Rev 03/2009

USA-Mt.Prospect, IL  
Canada  
[www.rauland.com](http://www.rauland.com)

• 800-752-7725  
• 905-607-2335

• Fax 800-217-0977  
• Fax 905-607-3554

**Rauland**  
**Rauland-Borg Corporation**