

MODEL: 354012 - STAFF ASSIST STATION



FEATURES

- Extra large back-lit button for easier activation
- Elapsed timer output
- Call-assurance LED
- Cancel button
- Plug-in connectors for easy service
- Continuous supervision of station
- Optional antimicrobial Bio-seal to cover buttons and allow for easy disinfecting of the station

SPECIFICATIONS

POWER REQUIRED: 6.33mA @ 18VDC

WEIGHT: 0.18 lbs (0.82 kg)

SIZE: W: 3.19" (8.113") (7.95 cm)

H: 4.25" (10.880 cm)

D: 0.6350" (1.627 cm) in back box: 0.50" (1.3 cm) off-wall

HOUSING & FINISH: High-impact molded Cylcoloy 2950 UL 94-5VB; light grey faceplate

CONTROLS: One (1) push button for call actuation,

One (1) Call-assurance LED, One (1) Cancel button

TERMINATIONS: Plug-on connector

BACKBOX REQUIREMENT: 1 device, Non-gangable, 3 1/2" deep, (i.e. Raco 561, Steel City 58371, ¾ R, or UL recognized equivalent metal backbox)

CERTIFICATION: UL/C-UL 1069, FCC Part 15 Class B, IEC60601-1 and IEC60601-1-2, CE Mark (LVD) (all Pending)

DESCRIPTION

The Staff Assist Station is a call pushbutton station providing the ability to place a staff call. Pressing the cancel button cancels the call. This station provides an output for an elapsed timer supporting a momentary or latched contact closure output. Using special buttons, the station can be customized for unique call priorities such as: "Code Pink," "Assist," "Bath," "Help," etc. The button can also be used for staff registration such as: "Nurse in Room", etc. The Staff Assist station is connected to its associated corridor light or domeless room controller and is continually supervised.

Rauland-Borg Corporation

Architects and Engineers Specifications available on disc. Specifications subject to change without notice.

USA • 800-752-7725 • Fax 847-679-4106
 CANADA • 905-607-2335 • Fax 905-607-3554
www.rauland.com

MODEL #354012
 05/2008

©Copyright 2008 Rauland-Borg Corporation / Printed in USA