MODEL: R5K Staff Station

Responder 5000

Rauland



፡ ር ና

FEATURES

- · Pushbutton for staff communication
- (1) Call Assurance LED and (1) Monitor LED
- Cancel button for station or room-wide cancel function
- · Optional antimicrobial Bio-seal to cover pushbuttons
- · Continuous supervision for station presence
- Surface mount for easy installation
- Mounting design accommodates a variety of single and dual gang backboxes

R5KSSTF

SPECIFICATIONS

Power Requirements: 15.5V DC @ 16 mA

Weight: 132 g (4.6 oz)

Size: W: 11.97 cm (4.71")

- H: 10.96 cm (4.31")
- **D:** 2.38 cm (0.94")

Housing and Finish: Polycarbonate ABS, UL 94-5VA; light gray faceplate.

Controls/Indicators: One (1) Call button, One (1) Call Assurance LED, One (1) Monitor LED, and One (1) Cancel button.

DESCRIPTION

The R5KSSTF Staff Station is usually mounted in staff locations where staff members are working. The station may also be used in patient areas such as therapy rooms or visitor lounges. The station provides communication to its covering console(s) via the call-in pushbutton. The station may also be used for audio monitoring of a designated area.

The station is connected to its associated corridor light or domeless controller and is continuously supervised for station presence. A "Trouble" message will also annunciate at the covering console(s) if the station is removed from the system or becomes non-functional.



Rauland A Division of AMETEK, Inc.

www.Rauland.com

Toll Free From Outside the U.S. +1 800 752 7725

+1 847 590 7100

Backbox Requirement: Surface mountable; compatible with European, North American, South American single and dual gang boxes.

Terminations: Plug on connector, CAT 5 and CAT 6 compatible

Certifications: Designed for compliance to ANSI/UL 1069, IEC 60950, CE, RoHS / WEEE Compliant. Assembled in a U.S. FDA Registered facility.

Architect and Engineer (A&E) Specifications available online at customerconnection.rauland.com Specifications subject to change without notice.