

Recommended stock spare parts and tools Cyber Ho 60/100/150

EBM000473.00	footswitch	
EBM000263.00	Panel female socket 8way to soldering for footswitch	
EBM000264.00	cable male plug, 8 poles to soldering for footswitch	
EAM000045	Interlock connector	
EBM000020	Interlock panel connector 5p female	
MBQ000190	Key	
MBQ000093	Keyswitch diam. 16mm	
EBQ002250	Electric contact for key	
MBQ000094	Emergency knob diam.16mm	
EBM000714	Electric contact for emergency button	
OBM000900	rod	
MAM000760.00	pumping chamber	
OBM000233	OC cavity mirror PL/PL AR/R=82%	
OBM000234	Rear cavity mirror HR /0deg	
OBM001561	aspheric lens (for focus in the fiber launch)	
OAM002266.00	Galvo mirror with mechanical holder	
OBQ020067	Green 5mW aiming diode	
EBM002050	Charger 3 kW 700Vdc	(for 60W and 100W)
EBM002052	Charger 4.5kW 700Vdc	(for 150W)
EAM000588.01	Discharger module	
MBQ001763	shutter motor counter clockwise	(for 60W)
MBQ001018	shutter motor clockwise	(for 100W and 150W)
IBQ000145	Filter insert for chillers P70390	(for 100W and 150W)
IBQ000146	cartridge for chiller P70390	(for 100W and 150W)
EBQ000100	Deionized cartridge	(Cyber Ho 60W)
OBM003592	lamp	
OAM001523	Blast shield	
EAQ001807.01	kit embedded	
EAQ000131	microcontroller board	
EAQ001809.01	Routing board cyber ho QSMK1701R00	
EAM000681.00	photodiode board	
EBQ003063	back light cable	
EBQ003062	display signal cable	
EBQ002709	display 12,1	
EBQ000488	RFID Modulator	
EAM000521	RFID interface board	
EAM001410.00	Antenna	

Tools

MBM006661.04	BMP0209 extension for alignment	(only for Cyber Ho 60)
MAQ000199.00	cross target for galvo mirror alignment tool	
2x MAQ000212.00	BMP0904 tool for optical bench alignment	
2 x OAF092099	200 micron Fiber for Service - NOT STERILE	
2 x OAF092799	272 micron Fiber for Service - NOT STERILE	
2 x OAF793619	365 micron Fiber for Service - not sterile - PRECISION	

Power Meter

SBQ000318	High Power Fan Cooled Thermal Sensors FL400A-LP2-50
SBQ000033	Scan head Ophir NOVA II display

Microscope

AAM000032.00	optical fibers microscope SUN-HMS200 - QS
--------------	---

For orders, prices and availability please contact spareparts@quantasystem.com